

PreciLabs

With **Direct**, **Absolute Multi-Dimensional**, **Multi-Axis position sensing**, **PreciLabs** patented technology

• is the **first industrial, multi-dimensional encoder** solution on the market

• increases resolution and accuracy of absolute position sensing thanks to the direct, contactless approach and goes beyond the fundamental limits of todays 1D linear and rotary encoders,

• enables high speed up to 100kHz

• and **improves reliability, safety** thanks to scalable redundancy of the patented 2D absolute codes

 Compensates static assembly tolerances and dynamic tolerances due to thermal and mechanical load variations in operational environment

PreciLabs' position sensing allows high-speed calculation of **2D absolute position** up to **100 kHz** with better than **0.01 um resolution** and with **submicrometer accuracy**. The position sensing enables also multi-dimensional measurements, e.g. **3D position of a light source by triangulation**.

PreciLabs provides a new paradigm for the encoder and position sensing markets with its one-fit-all 2D to 6D direct absolute position sensing, offering higher performance alternative in the operational environment, new features at lower cost than indirect multiple 1D encoder measurement in existing systems.

PreciLabs Advanced Position Sensors are offered as PreciLabs branded products for system integrators or White Label product to sensor manufacturers. The modularity of the design offers different connectivity protocols and the option to design custom enclosure around the PreciLabs sensor module hardware. For higher volume application, PreciLabs provides a reference design based on PreciLabs position sensing components and firmware.

PreciLabs SA

Absolute Direct 2D to 6D position sensing Micrometer precision "GPS"



Rue du Pontet 15; CH-1425 Onnens, Switzerland ; T +41 76 577 5726; info@precilabs.com; www.precilabs.com



PreciLabs

Technical advantages of PreciLabs technology:

- ✓ Offering one-fit-all solutions, nanometerprecision, 1D to 6D contactless absolute position measurement in working volumes from <1 cm³ up to >1 km³ and beyond
- ✓ 100-1,000 times higher frame-rate than existing imager-based solutions up to few 100 kHz, 10-100 times larger resolution in 1D to 6D position than COTS-based Multi-D encoders today.
- ✓ Sufficient redundancy for error detection and error correction up to 50% scale damage, and Safety Integrity Level certifications (SIL2,3)
- Single-sensor compensation of static and dynamic tolerances
- Miniaturization of the sensor down to 6x6x1 mm³ (size of the sensor ASIC)
- ✓ Advanced ASIC design and process with operating temperature up to 150°C
- Can be interfaced also with incremental encoder-based systems

Absolute Direct 2D to 6D position sensing Micrometer precision "GPS"

Parameters	Units	Perf.
max. Resolution (linear)	bits/m	27
max. Resolution (rotary)	bits/turn	24
Position refresh rate	frames/s	100'000
Scale speed (linear)	m/s	200
Scale speed (rotary)	rev./min (rpm)	50'000

Measuring 3D position, x, y, z of a light source in space:

Range: ~10mm ~100mm ~1000mm Resolution: 1-10nm 10-100nm 0.1-1 um *Measuring the angular position of a shaft using Hollow Shaft (HS) or End of Shaft (EOS) encoder, performance up to:*

22bit/rev and 1'000'000 rpm @ ø2mm, 26bit/rev and 100'000 rpm @ ø20mm, 27bit/rev and 50'000 rpm @ ø40mm, 29bit/rev and 9'000 rpm @ ø200mm

Measuring the 6D position of a Rotation Axis (e.g. turning, grinding machines) with better than 0.1 um (x,y,z) 0.1 urad (Rx,Ry,Rz) precision



PreciLabs SA

Rue du Pontet 15; CH-1425 Onnens, Switzerland ; T +41 76 577 5726; <u>info@precilabs.com</u>; <u>www.precilabs.com</u>



Absolute Direct 2D to 6D position sensing Micrometer precision "GPS"

Application examples:

- Innovative rotary encoders, End Of Shaft (EOS) and Hollow Shaft (HS) with high mounting tolerances
- LiDAR for autonomous vehicles, using beam-deflection, beam-steering, sub-urad precision 2D mirror position, compensating dynamic variations in challenging operational environment
- 2D-6D AR/VR control units or other instruments position sensing
- Medical robot assisted surgery, at very high-precision and reliability
- Miniature precision motors, e.g. BLDC, robotics
- CNC (Computer Numerical Control) machines (grinding, milling, turning,...) submicrometer, sub-micro-radian precision 6D rotation axis measurement
- Precision linear, rotary, 3D to 6D stages for laboratory or electronics, semiconductor manufacturing
- Hexapods, delta robots for precision assembly & metrology
- Industrial metrology, 3D scanning, CAD manufacturing verification, deflection monitoring, 3D trackers, walk-around scanners, inclinometers, touch trigger probes, scanning probes
- LASER displacement sensors
- Factory automation, 3D LASER profilers
- 2D, 3D printers
- Camera motion mechanisms
- 3D scanning and profilometry
- MEMS based accelerometers, gyroscopes
- Micro-radian precision sun-tracking
- Range finder with orientation
- 6D force sensor
- Torque sensor
- Systems for military and sports applications

		A	a ne little a	CINESS .		State of Lot of
	And Address	and successful to a	1111月1日日		0.000	A PROPERTY OFFICE
	12	and the second se	Contraction of the	CITY OF	and the story	
100	Contract of the local division of the	Contraction of the local division of the loc	L-Castrick	A CONTRACTOR OF	ALC: NOTE OF	And Address of the or and the second
	CONTRACTOR OF STREET,	Contraction of the	你没想要 到你。		四人面包	and the second second
	ALC NUMBER	account in the	Bear.	Contract of the local division of the local	10 200 10	STREET, DESCRIPTION
	- Applein	Structure 1	50 - 1 - 1 - 1 - 1 - 1 - 1 - 1 - 1 - 1 -	and the second		A STREET
	incom	ALC: NO DECISION	In A Manufacture	ALC: NOT THE OWNER OF	aller II	des alles a states
	and the second second	A PERSONAL PROPERTY AND	Local State	RTA BALLER		- 10 - 201
			語の現象語名		- 和和和	Selection and
1111	ALC: NOT THE	h all h	し、山口川市		「「「「「「「」」」	日本に自然
201	ALC: NO REAL PROPERTY.	1000	1	and a start	And Designed in the local division of the lo	All and the second second
1011	BIBBER PART	1990年	KRA BARTELEDA		The second second	A COLUMN TO A
	and the second	aligner et 112	ALC: NOT	distant and the	and the second second	PARTY OF THE OWNER
	10 M 1	1000	128		100	
The Party of the	COLUMN AND	- All states	100		111	STUDIES IN COLUMN
	1.5	100 C			121	CONTRACTOR OF
	100 1 100	STATISTICS STATISTICS	100			an anna an
	10.00	The second				
			10		111	
		ELSER TO Y	90 ·		111	Contraction of the local division of the loc
	and the second	No regime to the	100			COLUMN 2 MILLION
5-++ 1	65° (867)1	1510	ALC: NO DOLLARS	dia dia mandri di fasta		1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1
	in State	1000	ACC.			
121	and a state of	STILL STREET	10.000			
	Carlos and	展出 通知 1	1.00		100	111111
	Constraint.	and the second second	697			
N	a second					Constant in the local division of the
				100 1000	Contraction of the local division of the	in balling and

5x5mm PreciSen Asic Floorplan

